

U-POL

PRODUCTS

FASTGLAS

Glass Fibre Kit

Description

FASTGLAS is a polyester resin kit, containing resin, hardener, glass fibre, mixing cup, and plastic gloves.

FASTGLAS has been developed for the repair of holes, splits, cracks and tears in most materials including metal, wood, hard plastic, bricks etc.

FASTGLAS can also be used as a construction material to manufacture storage tanks etc.

FASTGLAS offers perfect adhesion to most surfaces and is a solid base for most paint systems.

FASTGLAS can be used

- to repair, construct and create.
- It is resilient, permanent, waterproof.
- Has 1000's of uses
- Is quick and easy to use

Surface preparation

Prepare well. Surface must be clean, dry, and free from all traces of grease, loose matter and rust. Abrade with P40 paper.

Cut sufficient matting in order to cover the surface.

Hardener

To activate **FASTGLAS**, use 2% to 3% of

FASTGLAS hardener. Mix well immediately.

Do not use in temperatures below 5°C. Gel time varies depending on the ambient temperature.

U-POL

PRODUCTS

Thinner

Dilution of this product is not recommended.
Clean tools immediately after use in cellulose thinners or acetone.

Application

Paint the prepared area with activated resin using an old brush.

Apply a workable size of mat to the area and then using a stiff brush, stipple the glass fibre until it is "wetted".

Clean tools immediately.

Leave the resin to dry and repeat the application with more strips of mat until the desired effect is achieved.

Pot life

The activated resin mixture remains useable and liquid for up to 5 minutes at 20 degrees C.

Over-painting

Sand, clean and dry completely. In order to fill any pin holes or imperfections on the surface, use a **U-Pol** polyester body filler. **FASTGLAS** can be re-covered by the majority of primers and paint systems.

Product code and contents

GL/LA/D Kit contains, RE/LA, hardener, glass fibre matting, mixing sticks, gloves, measuring cup.

GL/SM/D Kit contains, RE/SM hardener, glass fibre matting, mixing sticks, gloves, measuring cup.

Refill codes

RE/XL Can of resin 1L.
RE/LA Can of resin 500ml.
RE/SM Can of resin 250ml.
HAR/BLM FASGLAS hardener.
GFT Mat 0.5M²
GFM Tissue 0.5M²